

The Better Pex Header

Reduced/Closed Pex Headers 1" Pipe run, with 2,3,4,5,6,7,8,9,10,11, or 12 1/2" Crimpex (ASTM F877) fittings on **2" centres**. Closed one end and reduced 3/4" female sweat on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
---------------------	-----------------	--------------------	----------------	-----------------

SX1005002RC	1"	1/2" PEX	2	10
SX1005003RC	1"	1/2" PEX	3	10
SX1005004RC	1"	1/2" PEX	4	10
SX1005005RC	1"	1/2" PEX	5	10
SX1005006RC	1"	1/2" PEX	6	10
SX1005007RC	1"	1/2" PEX	7	10
SX1005008RC	1"	1/2" PEX	8	10
SX1005009RC	1"	1/2" PEX	9	10
SX1005010RC	1"	1/2" PEX	10	10
SX1005011RC	1"	1/2" PEX	11	10
SX1005012RC	1"	1/2" PEX	12	10

Variations available to the above at an additional charge.

1/2" Lead free (C69300 ECO Brass) Pex

1/2" Everloc Pex

3/4" Crimpex

Expanded/Closed Pex Header

1" Pipe run, with 2,3,4,5,6,7,8,9,10,11, or 12 1/2" Crimpex (ASTM F877) fittings on **1 1/2" centres**. Closed on one end and expanded to 1" female sweat on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
---------------------	-----------------	--------------------	----------------	-----------------

CX1005002EXC	1"	1/2" PEX	2	10
CX1005003EXC	1"	1/2" PEX	3	10
CX1005004EXC	1"	1/2" PEX	4	10
CX1005005EXC	1"	1/2" PEX	5	10
CX1005006EXC	1"	1/2" PEX	6	10
CX1005007EXC	1"	1/2" PEX	7	10
CX1005008EXC	1"	1/2" PEX	8	10
CX1005009EXC	1"	1/2" PEX	9	10
CX1005010EXC	1"	1/2" PEX	10	10
CX1005011EXC	1"	1/2" PEX	11	10
CX1005012EXC	1"	1/2" PEX	12	10

Variations available to the above at an additional charge.

1/2" Lead free (C69300 ECO Brass) Pex

1/2" Everloc Pex

3/4" Crimpex

Plain/Closed Pex Headers 1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12 1/2" Crimpex (ASTM F877) fittings on **2"centres**. Closed one end and plain on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PL	1"	1/2" PEX	2	10
SX1005003PL	1"	1/2" PEX	3	10
SX1005004PL	1"	1/2" PEX	4	10
SX1005005PL	1"	1/2" PEX	5	10
SX1005006PL	1"	1/2" PEX	6	10
SX1005007PL	1"	1/2" PEX	7	10
SX1005008PL	1"	1/2" PEX	8	10
SX1005009PL	1"	1/2" PEX	9	10
SX1005010PL	1"	1/2" PEX	10	10
SX1005011PL	1"	1/2" PEX	11	10
SX1005012PL	1"	1/2" PEX	12	10

Variations available to the above at an additional charge.

1/2" Lead free (C69300 ECO Brass) Pex

1/2" Everloc Pex

3/4" Crimpex

Closed/Pex Ends on Pex Headers 1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12 1/2" Crimpex (ASTM F877) fittings, **2"centres**. Closed one end and 3/4"brass pex the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PC	1"	1/2" PEX	2	10
SX1005003PC	1"	1/2" PEX	3	10
SX1005004PC	1"	1/2" PEX	4	10
SX1005005PC	1"	1/2" PEX	5	10
SX1005006PC	1"	1/2" PEX	6	10
SX1005007PC	1"	1/2" PEX	7	10
SX1005008PC	1"	1/2" PEX	8	10
SX1005009PC	1"	1/2" PEX	9	10
SX1005010PC	1"	1/2" PEX	10	10
SX1005011PC	1"	1/2" PEX	11	10
SX1005012PC	1"	1/2" PEX	12	10

Variations available to the above at an additional charge.

1/2" Lead free (C69300 ECO Brass) Pex

1/2" Everloc Pex

3/4" Crimpex

3/4" Pex at Each End of Pex Header 1"Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12 1/2" Crimpex (ASTM F877) fittings on **2"centres** with 3/4"brass pex each end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PP	1"	1/2" PEX	2	10
SX1005003PP	1"	1/2" PEX	3	10
SX1005004PP	1"	1/2" PEX	4	10
SX1005005PP	1"	1/2" PEX	5	10
SX1005006PP	1"	1/2" PEX	6	10
SX1005007PP	1"	1/2" PEX	7	10
SX1005008PP	1"	1/2" PEX	8	10
SX1005009PP	1"	1/2" PEX	9	10
SX1005010PP	1"	1/2" PEX	10	10
SX1005011PP	1"	1/2" PEX	11	10
SX1005012PP	1"	1/2" PEX	12	10

Variations available to the above at an additional charge.

1/2" Lead free (C69300 ECO Brass) Pex

1/2" Everloc Pex

3/4" Crimpex


Pex Shut Off Valve Headers 1" or 1 1/4" Pipe run with 2,3 or 4 1/2" Crimpex miniball valve expanded to coupling size one end and plain the other end on **2"centres**.



Stock Number	Pipe Run	Outlet Size	Outlets	Unit/Box
CVP1005002	1"	1/2"	2	5
CVP1005003	1"	1/2"	3	5
CVP1005004	1"	1/2"	4	5
CVP1005006	1"	1/2"	6	5
CVP1255002	1 1/4 "	1/2"	2	4
CVP1255003	1 1/4 "	1/2"	3	4
CVP1255004	1 1/4 "	1/2"	4	4

Variations available to the above at an additional charge.
 1/2" Lead free (C69300 ECO Brass) Pex Valves
 3/4" Crimpex Valves

Pex Balancing Valves Headers 1" or 1 1/4" Pipe run with 2,3 or 4 1/2" Crimpex miniball balancing valve. Expanded to coupling size one end and plain the other end on **2"centres**.




Stock Number	Pipe Run	Outlet Size	Outlets	Unit/Box
CVBP1005002	1"	1/2"	2	5
CVBP1005003	1"	1/2"	3	5
CVBP1005004	1"	1/2"	4	4
CVBP1255002	1 1/4 "	1/2"	2	3
CVBP1255003	1 1/4 "	1/2"	3	3
CVBP1255004	1 1/4 "	1/2"	4	3

[Click Here](#) for a Printable version of this page.



Ph: 780-349-6511 Fax: 780-349-4232
 Email: info@customtee.com



Home	Sales Reps and Distributors	72 inch Headers	Specialty Headers	End Caps, Reduced Ends & Tees
About Alberta Custom Tee	The Alberta Custom Tee Advantage	The Better Pex Header	Custom Extrusions	Outlet Tools