

The Better Pex Header

Reduced/Closed Pex Headers

1" Pipe run, with 2,3,4,5,6,7,8,9,10,11, or 12

1/2" Crimpex (ASTM F877) fittings on 2" centres.

Closed one end and reduced 3/4" female sweat on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002RC	1"	1/2" PEX	2	10
SX1005003RC	1"	1/2" PEX	3	10
SX1005004RC	1"	1/2" PEX	4	10
SX1005005RC	1"	1/2" PEX	5	10
SX1005006RC	1"	1/2" PEX	6	10
SX1005007RC	1"	1/2" PEX	7	10
SX1005008RC	1"	1/2" PEX	8	10
SX1005009RC	1"	1/2" PEX	9	10
SX1005010RC	1"	1/2" PEX	10	10
SX1005011RC	1"	1/2" PEX	11	10
SX1005012RC	1"	1/2" PEX	12	10

Plain/Closed Pex Headers

1" Pipe run with 2,3,4,5,6,7,8,9,10,11 or
12 1/2" Crimpex (ASTM F877) fittings on
2" centres. Closed one end and plain on the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PL	1"	1/2" PEX	2	10
SX1005003PL	1"	1/2" PEX	3	10
SX1005004PL	1"	1/2" PEX	4	10
SX1005005PL	1"	1/2" PEX	5	10
SX1005006PL	1"	1/2" PEX	6	10
SX1005007PL	1"	1/2" PEX	7	10
SX1005008PL	1"	1/2" PEX	8	10
SX1005009PL	1"	1/2" PEX	9	10
SX1005010PL	1"	1/2" PEX	10	10
SX1005011PL	1"	1/2" PEX	11	10
SX1005012PL	1"	1/2" PEX	12	10

Closed/Pex Ends on Pex Headers

1" Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12


1/2" Crimpex (ASTM F877) fittings, 2" centres.

Closed one end and 3/4" brass pex the other end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PC	1"	1/2" PEX	2	10
SX1005003PC	1"	1/2" PEX	3	10
SX1005004PC	1"	1/2" PEX	4	10
SX1005005PC	1"	1/2" PEX	5	10
SX1005006PC	1"	1/2" PEX	6	10
SX1005007PC	1"	1/2" PEX	7	10
SX1005008PC	1"	1/2" PEX	8	10
SX1005009PC	1"	1/2" PEX	9	10
SX1005010PC	1"	1/2" PEX	10	10
SX1005011PC	1"	1/2" PEX	11	10
SX1005012PC	1"	1/2" PEX	12	10

3/4" Pex at Each End of Pex Header
 1" Pipe run with 2,3,4,5,6,7,8,9,10,11 or 12 1/2" Crimpex (ASTM F877) fittings on 2" centers with 3/4" brass pex each end.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
SX1005002PP	1"	1/2" PEX	2	10
SX1005003PP	1"	1/2" PEX	3	10
SX1005004PP	1"	1/2" PEX	4	10
SX1005005PP	1"	1/2" PEX	5	10
SX1005006PP	1"	1/2" PEX	6	10
SX1005007PP	1"	1/2" PEX	7	10
SX1005008PP	1"	1/2" PEX	8	10
SX1005009PP	1"	1/2" PEX	9	10
SX1005010PP	1"	1/2" PEX	10	10
SX1005011PP	1"	1/2" PEX	11	10
SX1005012PP	1"	1/2" PEX	12	10

Pex Shut Off Valve Headers
 1" or 1 1/4" Pipe run with 2,3 or 4 1/2" Crimpex miniball valve expanded to coupling size one end and plain the other end on 2" centers.



<i>Stock Number</i>	<i>Pipe Run</i>	<i>Outlet Size</i>	<i>Outlets</i>	<i>Unit/Box</i>
CVP1005002	1"	1/2"	2	5
CVP1005003	1"	1/2"	3	5
CVP1005004	1"	1/2"	4	5
CVP1255002	1 1/4 "	1/2"	2	4
CVP1255003	1 1/4 "	1/2"	3	4
CVP1255004	1 1/4 "	1/2"	4	4

Pex Balancing Valves Headers

1" or 1 1/4" Pipe run with 2, 3 or 4 1/2" Crimpex miniball balancing valve. Expanded to coupling size one end and plain the other end on 2" centers..




CVBP1005002	1"	1/2"	2	5
CVBP1005003	1"	1/2"	3	5
CVBP1005004	1"	1/2"	4	4
CVBP1255002	1 1/4 "	1/2"	2	3
CVBP1255003	1 1/4 "	1/2"	3	3
CVBP1255004	1 1/4 "	1/2"	4	3

[Click Here](#) for a Printable version of this page.



Ph: 780-349-6511 Fax: 780-349-4232
 Email: info@customtee.com



Home	Sales Reps and Distributors	72 inch Headers	Specialty Headers	End Caps, Reduced Ends & Tees
About Alberta Custom Tee	The Alberta Custom Tee Advantage	The Better Pex Header	Custom Extrusions	Outlet Tools